

O-ring, d2=3,0MM Rubber NBR 70° Shore A d2=3,0MM 12,0MM



Artikelnummer	38810.012.001
Merk	-
UBB	950357197157
UNSPSC	27111900
EAN	8715492785732
PKG. van 50	Alleen volledige verpakkingen

Technische parameters

Diameter	12 mm
Kleur	Zwart
Materiaalsoort	Rubber
Materiaalsoort Technisch	NBR 70° Shore A
Info	d2=3,0MM

Standaarden

Technische specificatie

d1	12
D (mm)	12
Dikte	3

Technische tekening

