



FISCHER Hinged pipe clamp FGRS Plus 25 - 30 M 8/M10

Artikelnummer	79433FIS
Merk	-
UBB	500616848536
UNSPSC	31162905
EAN	4006209794333
PKG. van 100	Alleen volledige verpakkingen

Technische parameters

Info	N = Max. recom. static load (centr. tension) [kN].
------	--

Standaarden

Technische specificatie

Technische tekening

