



Veiligheidsanker type FH II-B M12X75/25

Artikelnummer	97636FIS
Merk	-
UBB	500616711577
UNSPSC	31162101
EAN	4006209976364
PKG. van 1	Alleen volledige verpakkingen

Technische parameters

Diameter	M12
----------	-----

Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should

Standaarden

FABORY

comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Technische specificatie

Technische tekening

