



Spring-type straight pin (spiral pin) coiled, heavy duty ASME ASME B18.8.2 Spring steel SAE 1070 3/16X3/4

Article number	U39150.018.0075
Brand	-
UBB	500626365554
UNSPSC	31162400
EAN	8715494004299
PKG. of 50	Full Box Only

Technical Parameters

Length	3/4 Inch
A (nom.)	0.1875
Material	Spring steel
Material technical	SAE 1070
Info	Warning: electroplating of these products may cause hydrogen embrittlement.V = minimum double shear load in lb.

Standards

ASME	B18.8.2
------	---------

Technical Specification

A (max.)	0.202
B (max.)	0.182
C (ref.)	0.055
A (min.)	0.194
V	4500

Technical Drawing

