

O-ring, d2=2,4MM Rubber NBR 70° Shore A d2=2,4MM 5,3MM



Artikelnummer	38806.005.301
Merk	-
UBB	950357251426
UNSPSC	27111900
EAN	8715492784544
PKG. van 50	Alleen volledige verpakkingen

Technische parameters

Diameter	5.3 mm
Kleur	Zwart
Materiaalsoort	Rubber
Materiaalsoort Technisch	NBR 70° Shore A
Info	d2=2,4MM

Standaarden

Technische specificatie

d1	5.3
D (mm)	5.3
Dikte	2.4

Technische tekening

