



Hexalobular socket head cap screw ISO 14580 Stainless steel A2 50 M4X12

Article number	51122.040.012
Brand	-
UBB	500571833085
UNSPSC	31161501
EAN	8715494113113
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M4
Lengte	12 mm
Klasse	50
Aandraaivoorziening	T-ster
Kopsoort	Lage cilinderkop
Materiaalsoort	Roestvaststaal
Materiaalsoort Technisch	A2
Draadsoort	Metrische schroefdraad

Standards

ISO	14580
-----	-------

Technical Specification

b (min.)	38
d-D	M4
dk(max.)	7
k (max.)	3.1
L (mm)	12
P	0.7
Sleutel	20

Technical Drawing

