

SPIT Inslaganker SA Roestvaststaal (RVS) A4 M8



Artikelnummer	70875.080.001
Merk	-
UBB	950352934307
UNSPSC	31162101
EAN	8715492906182
PKG. van 100	Alleen volledige verpakkingen

Technische parameters

d ₁	M8
Remarks	Inslagankers type GRIP SA dienen gemonteerd te worden met inslagpen type S (zie artikelgroep 70967). Allowable design load N _{rd,c} (kN) for a single anchor in concrete C20/25 without influence of edge distances or other anchors. Allowable load includes the safety factor #m = 1,5, see approval.
Diameter (d-D)	M8
Materiaalsoort	Roestvaststaal (RVS)
Materiaalsoort Technisch	A4
Draadsoort	Metrische schroefdraad
Type no.	SA

Standaarden

Technische specificatie

a	13
---	----

Technische tekening

Beton \geq C20/25	5.5
d_2	10
Boordiepte (min.)	33
Boor \varnothing	10
Lengte (L) (mm)	30
Aandraaimoment (Nm)	10

