



M10 S/20

Artikelnummer	90251FIS
Merk	-
UBB	500616785589
UNSPSC	31161607
EAN	4006209902516
PKG. van 25	Alleen volledige verpakkingen

Technische parameters

Diameter	10 mm
Lengte	90 mm
Belangrijkste kenmerken	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TA M can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l s : Screw length l s = Length of fixing + Thickness of fixture t fix + Thickness of washer.
ETA-approval	Ja
Info	do= Nominal diameter of drill bit.dd= Embedment depth.df= Anchor diameter.fs= Head

Standaarden

diameter.Ws=
Setting tool
diameter.hef=
Effective anchorage
depth.tfix= Grip
range.kN =
Allowable load in kN.

Technische specificatie

Technische tekening

