

M20X290



Artikelnummer	90293FIS
Merk	-
UBB	500616697149
UNSPSC	31161601
EAN	4006209902936
PKG. van 10	Alleen volledige verpakkingen

Technische parameters

Diameter	M20
Lengte	290 mm
ETA-approval	Ja

Info

Ccr, N =
Characteristic
Edge distance
(tensile).Cmin. =
Minimum edge
distance (tensile).df
= Hole diameter
in fixture.do =
Hole diameter in
substrate.hef =
Effective embedment
depth.hmin =
Minimum substrate
thickness.ho =
Minimum hole
depth.Scr, N =
Characteristic
spacing.Concrete
C20/25
recommended load
for non-cracked
concrete.The
allowable load is only
valid for AcryMaxx
Chemical Mortar
in combination
with Anchor studs,
steel grade 5.8.The
allowable load is
valid for one single

Standaarden

FABORY

anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische specificatie

Technische tekening

