



Ancoragem perno tipo FH II-S 12/15 SK

Referência	9E860633
Marca	-
UBB	500636503574
UNSPSC	31162101
EAN	4042205122589
Emb. de 1	Apenas embalagem completa

Parâmetros técnicos

Conteúdo do conjunto	2 x FH II 12/10 S
----------------------	-------------------

Info

do = Nominal diameter of drill bit. Min. td = Recommended drilling depth. hef = Effective anchorage depth. tfix = Grip range. s = Width across flats. kN = Load in kN. The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final

Normas

FABORY

calculations should
comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Especificação técnica

Desenho técnico

