



KNIP ALICAT REDO 2627-200MM CURVED

Referência	K1026.720.200
Marca	-
UBB	419100384660
UNSPSC	27112148
EAN	4003773016090
Emb. de 1	Apenas embalagem completa

Parâmetros técnicos

Versão	Cromado & isolamento de imersão, testado de vde
Capacidade	2.2
Comprimento total	200
Observações	High loaded, elastic precision points. Half-round, long jaws. Cutting edges additionally induction hardened, cutting edge hardness approximately 61 HRc. Vanadium steel, oil-hardened and tempered. Style 1: straight jaws. Style 2: bent jaws. Finish 1 = Head polished. Handles plastic coated. Finish 2 = Head polished. Handles with two-colour dual component sleeves. Finish 3 = Plier chrome plated. Handles plastic coated. Finish 5 = Plier chrome plated. Handles

Normas

ISO	5745
-----	------

with two-colour
dual component
sleeves. Finish 6 =
Plier chrome plated.
Handles insulated
with two-colour dual
component sleeves
1000 V VDE-tested
DIN EN/IEC 60900.
Finish 7 = Plier
chrome plated.
Handles dipped
plastic insulated
1000 V VDE-tested
DIN EN/IEC60900.