

#urub cu cap hexagonal par#ial filetat DIN 931 O#el Simplu 8.8 M8X85



Cod Articol	01000.080.085
Marcă	-
UBB	951351606466
UNSPSC	31161620
EAN	8715492007469
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric
Diametru (d-D)	M8
Lungime (L) (mm)	85

Standarde

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M

Specificatii tehnice

b (min.): 125mm<L≤200mm	28
b (min.): L≤125mm	22
k	5.3
P	1.25
s	13

Desen tehnic

