

## #urub cu cap hexagonal par#ial filetat DIN 931 O#el Simplu 8.8 M20X280



Cod Articol	01000.200.280
Marcă	-
UBB	950351017161
UNSPSC	31161620
EAN	8715492009418
PKG. of 10	Exclusiv împachetare

### Parametri tehnici

Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric
Diametru (d-D)	M20
Lungime (L) (mm)	280

### Standarde

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

### Specificatii tehnice

b (min.): 125mm<L≤200mm	52
b (min.): L>200mm	65
b (min.): L≤125mm	46
k	12.5
P	2.50
s	30

### Desen tehnic

