

#urub cu cap hexagonal par#ial filetat DIN 931 O#el Simplu 8.8 M30X140



Cod Articol	01000.300.140
Marcă	-
UBB	950351024829
UNSPSC	31161620
EAN	8715492010506
PKG. of 10	Exclusiv împachetare

Parametri tehnici

Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric
Diametru (d-D)	M30
Lungime (L) (mm)	140

Standarde

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014

Specificatii tehnice

b (min.): 125mm<L≤200mm	72
b (min.): L>200mm	85
b (min.): L≤125mm	66
k	18.7
P	3.50
s	46

Desen tehnic

