

#urub cu cap hexagonal par#ial filetat DIN 931 O#el Simplu 8.8 M36X190



Cod Articol	01000.360.190
Marcă	-
UBB	950351029463
UNSPSC	31161620
EAN	8715492011138
PKG. of 2	Exclusiv împachetare

Parametri tehnici

Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric
Diametru (d-D)	M36
Lungime (L) (mm)	190

Standarde

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Specificatii tehnice

b (min.): 125mm<L≤200mm	84
b (min.): L>200mm	97
b (min.): L≤125mm	78
k	22.5
P	4
s	55

Desen tehnic

