


#urub cu cap hexagonal par#ial filetat DIN 931 O#el Simplu 8.8 M42X340



Cod Articol	01000.420.340
Marcă	-
UBB	952351209871
UNSPSC	31161620
EAN	8715492011763
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric
Diametru (d-D)	M42
Lungime (L) (mm)	340

Standarde

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014

Specificatii tehnice

b (min.): 125mm<L≤200mm	96
b (min.): L>200mm	109
b (min.): L≤125mm	90
k	26
P	4.50
s	65

Desen tehnic

