



#uruburi fit cap hexagonal cu filet scurt DIN 609 O#el Simplu 8.8 M8X60X44,6

Cod Articol	01040.080.060
Marcă	-
UBB	500644607318
UNSPSC	31161620
EAN	8717077009288
PKG. of 25	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M8
Lungime (L) (mm)	60
Lg (max.)	44.6
Clasă	8.8
Tip antrenare	Hexagonal
Forma de cap	Cap hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric

Standarde

DIN	609
-----	-----

Specificatii tehnice

b:50mm<L≤150mm	16.5
b (min.): L>150mm	21.5
b:L≤50mm	14.5
d _s (k6)	9 (9,001-9,010)
k	5.3
P	1.25
s	13
Toleran#ă burghiu ø	H7

Desen tehnic

