



Set de asamblări structurale - șurub hexagonal parțial filetat & piuliță hexagonală EN 15048 Oțel Zincat 8.8/8 M16X55

Cod Articol	01222.160.055
Marcă	-
UBB	500574452446
UNSPSC	31161620
EAN	8715494305884
PKG. of 50	Exclusiv împachetare

Parametri tehnici

Diameter	M16
Lungime	55 mm
Clasă	8.8/8
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel
Direcție filet	Dreapta
Tratament suprafață	Zincat
Filete	Filet metric

Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

Standarde

EN	15048
ISO	4014/4032

bolting according to EN 15048-1 are compliant with the CPR. Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are packaged together in single sealed boxes. A Declaration of Performance (DoP) is available.

Specificatii tehnice

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	55
m (max.)	14.8
P	2
s	24

Desen tehnic

