

Șurub cu cap hexagonal, filet metric ISO DIN 933 Oțel Zincat termic 8.8 M6X30

Cikkszám	01410.060.030
Márka	-
UBB	500574308408
UNSPSC	31161620
EAN	8715494301657
csom. 500	Csak bontatlan csomagban

Műszaki adatok

Diameter	M6
Lungime	30 mm
Clasă	8.8
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel
Direcție filet	Dreapta
Tratament suprafață	Zincat termic
Filete	Filet metric

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Szabványok

NEN	1568
ISO	4017
ASME	B18.2.3.1M
NF	E25-114
DIN	933

Műszaki specifikációk

d-D	M6
k	4
L (mm)	30

Műszaki rajz

P	1
S	10

