

#uruburi inbus ISO4762 zincate ISO 4762 O#el Zincat 10.9 M3X16



Cod Articol	07027.030.016
Marcă	-
UBB	500650814600
UNSPSC	31162400
EAN	8717077295926
PKG. of 500	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M3
Lungime (L) (mm)	16
Clasă	10.9
Tip antrenare	Locaş hexagonal
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Zincat
Filete	Filet metric

Standarde

BS	4168-1
DIN	912
NF	E25-125
ISO	4762
ASME	B18.3.1M

Specificatii tehnice

b	18
d _k (max.)	5.5
Filet complet L ≤	20
k (max.)	3
s	2.5

Desen tehnic

