



Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M4X6

Article number	07150.040.006
Brand	-
UBB	950351436684
UNSPSC	31161518
EAN	8715492068569
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

ISO	7380-1
NF	≈E25-126
BS	≈4168-6
ASME	≈B18.3.4M

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

d-D	M4
dk (max.)	7.6
Full thread if $L \leq$	16
k (max.)	2.2
L (mm)	6
P	0.7
s	2.5

Technical Drawing

