



## #urub cu cap torbant #i guler pătrat, par#ial filetat DIN 603 O#el Simplu 8.8 M6X50

Cod Articol	08310.060.050
Marcă	-
UBB	950351617515
UNSPSC	31161612
EAN	8715492558282
PKG. of 200	Exclusiv împachetare

### Parametri tehnici

Threaded pitch (P)	1
Diametru (d-D)	M6
Lungime (L) (mm)	50
Clasă	8.8
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric

### Standarde

BS	≈4933
DIN	603
ISO	≈8677

### Specificatii tehnice

b (min.): 125mm<L≤200mm	24
b (min.): L≤125mm	18
d <sub>k</sub> (max.)	16.55
k (max.)	3.88
P	1
f <sub>n</sub> (max.)	4.6
V <sub>n</sub> (max.)	6.48

### Desen tehnic

