



Șurub cap torbant & piuliță hexagonală, filet supradimensionat DIN 603/555 Oțel Zincat termic 4.8 M8X60

Cod Articol	08420.080.060
Marcă	-
UBB	951351381474
UNSPSC	31161612
EAN	8715492560933
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diameter	M8
Lungime	60 mm
Clasă	4.6
Material	Oțel
Direcție filet	Dreapta
Tratament suprafață	Zincat termic
Filete	Filet metric

Info

The property class of the corresponding nuts is |4| as a minimum. Depending the supplier material class can differ (4.6 or 4.8) Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been

Standarde

DIN	603/555
NF	≈E27-351/E25-402
ISO	≈8677/4034
BS	≈4933/3692
NEN	≈303/697

Specificatii tehnice

b (min.): 28
125mm $L \leq 200$ mm

b (min.): L200mm 41

b (min.): $L \leq 125$ mm 22

d-D M8

dk (max.) 20.65

k (max.) 4.88

L (mm) 60

m 6.5

P 1.25

fn (max.) 5.6

s 13

Vn (max.) 8.58

Desen tehnic

