

Șurub cu cap hexagonal complet filetat ISO 4017 Oțel (AD-W7) Zincat 5.6 pentru vase de presiune M6X30

Cod Articol	08761.060.030
Marcă	-
UBB	500648346954
UNSPSC	31161620
EAN	8717077244610
PKG. of 500	Exclusiv împachetare

Parametri tehnici

Diameter	M6
Lungime	30 mm
Clasă	5.6
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel (AD-W7)
Direcție filet	Dreapta
Tratament suprafață	Zincat
Filete	Filet metric

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standarde

ISO	4017
NEN	1568
ASME	B18.2.3.1M
NF	E25-114
DIN	933

FABORY

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Specificatii tehnice

d-D	M6
k	4
L (mm)	30
P	1
s	10

Desen tehnic

