

Șurub cu cap hexagonal complet filetat ISO 4017 Oțel (AD-W7) Zincat 5.6 pentru vase de presiune M8X60

Cod Articol	08761.080.060
Marcă	-
UBB	500648348364
UNSPSC	31161620
EAN	8717077244757
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diameter	M8
Lungime	60 mm
Clasă	5.6
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel (AD-W7)
Direcție filet	Dreapta
Tratament suprafață	Zincat
Filete	Filet metric

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standarde

DIN	933
ASME	B18.2.3.1M
ISO	4017
NEN	1568
NF	E25-114

FABORY

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Specificatii tehnice

d-D	M8
k	5.3
L (mm)	60
P	1.25
s	13

Desen tehnic

