

#tifturi filetate ISO2342 loca# crestat par#ial filetate ISO 2342 O#el Simplu 14H M8X20



Cod Articol	20055.080.020
Marcă	-
UBB	500651015736
UNSPSC	31162400
EAN	8717077316096
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M8
Lungime (L) (mm)	20
Clasă	14H
Tip antrenare	Crestat
Material (lung)	O#el
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu
Filete	Filet metric

Standarde

ISO	2342
-----	------

Specificatii tehnice

b	9.6
d _s	8
n	1.2

Desen tehnic

