



Slotted cheese head, turned ISO 1207 Oțel Simplu M1X8

Cod Articol	24500.010.008
Marcă	-
UBB	500648419488
UNSPSC	31161504
EAN	8717077224087
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Diameter	M1
Lungime	8 mm
Tip antrenare	Crestat
Forma de cap	Cap cilindric
Material	Oțel
Tratament suprafață	Simplu
Filete	Filet metric
Info	ISO 1207, turned

Standarde

ISO	1207
-----	------

Specificatii tehnice

d-D	M1
Thread length (min.)	25
dk (max.)	2
Filet complet $L \leq$	30
k (max.)	0.7
L (mm)	8
n	0.25
P	0.25
t (min.)	0.25

Desen tehnic

