

#urub cu cap cilindric, loca# crestat DIN 84 O#el Zincat 4.8 M2X6



Cod Articol	24520.020.006
Marcă	-
UBB	950353111251
UNSPSC	31161504
EAN	8715492629678
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M2
Lungime (L) (mm)	6
Clasă	4.8
Tip antrenare	Crestat
Forma de cap	Cap cilindric
Material (lung)	O#el
Tratament al suprafeței	Zincat
Filete	Filet metric

Standarde

ASME	≈B18.6.7M
BS	≈4183
ISO	≈1207
NF	≈E25-127
DIN	84

Specificatii tehnice

Thread length (min.)	25
d_k (max.)	3.8
Filet complet $L \leq$	30
k (max.)	1.3
n	0.5
P	0.40
t (min.)	0.5

Desen tehnic

