

#urub cu cap cilindric, loca# crestat DIN 84 O#el Zincat 4.8 M8X12



Cod Articol	24520.080.012
Marcă	-
UBB	950353120658
UNSPSC	31161504
EAN	8715492631138
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M8
Lungime (L) (mm)	12
Clasă	4.8
Tip antrenare	Crestat
Forma de cap	Cap cilindric
Material (lung)	O#el
Tratament al suprafeței	Zincat
Filete	Filet metric

Standarde

NF	E25-127
ASME	B18.6.7M
DIN	84
ISO	1207
BS	4183

Specificatii tehnice

d_k	13
Filet complet $L \leq$	40
k	5
n	2
P	1.25

Desen tehnic

