

#urub cu cap rotund, loca# crestat DIN 85 O#el Zincat 4.8 M3X20



Cod Articol	24640.030.020
Marcă	-
UBB	950353152909
UNSPSC	31161504
EAN	8715492637031
PKG. of 500	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M3
Lungime (L) (mm)	20
Clasă	4.8
Tip antrenare	Crestat
Forma de cap	Cap cilindric
Material (lung)	O#el
Tratament al suprafeței	Zincat
Filete	Filet metric

Standarde

BS	4183
DIN	85
ISO	1580
NF	E25-128
ASME	B18.6.7M

Specificatii tehnice

d_k	6
Filet complet $L \leq$	30
k	1.8
n	0.8
P	0.50

Desen tehnic

