

#urub cu cap rotund, loca# crestat DIN 85 O#el Zincat 4.8 M6X30



Cod Articol	24640.060.030
Marcă	-
UBB	950353155712
UNSPSC	31161504
EAN	8715492637710
PKG. of 200	Exclusiv împachetare

Parametri tehnici

Diametru (d-D)	M6
Lungime (L) (mm)	30
Clasă	4.8
Tip antrenare	Crestat
Forma de cap	Cap cilindric
Material (lung)	O#el
Tratament al suprafeței	Zincat
Filete	Filet metric

Standarde

DIN	85
BS	4183
ASME	B18.6.7M
NF	E25-128
ISO	1580

Specificatii tehnice

d_k	12
Filet complet $L \leq$	40
k	3.6
n	1.6
P	1

Desen tehnic

