



12/140 (12X236)

Cod Articol	45581FIS
Marcă	-
UBB	500616649132
UNSPSC	31162101
EAN	4006209455814
PKG. of 10	Exclusiv împachetare

Parametri tehnici

Diameter	M12
Lungime	189 mm
Caracteristici cheie	<p>Functioning - The FBN II is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS bolt anchor setting tool.</p>

Standarde

Aprobare ETA

Yes

Info	<p>do = Nominal diameter of drill bit.</p> <p>tfix = Grip range.</p> <p>hef = Effective anchorage depth.</p> <p>Min. td = Recommended drilling depth.</p> <p>kN = Load in kN.</p> <p>The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account.</p> <p>When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.</p> <p>Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.</p>
------	---

Specificatii tehnice

Desen tehnic

