



16X180

Cod Articol	45799FIS
Marcă	-
UBB	500616731120
UNSPSC	31162101
EAN	4006209457993
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Caracteristici cheie	<p>Functioning - The FWA is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS setting tool.</p>
----------------------	---

Standarde

Info	<p>do = Nominal diameter of drill bit.tfix = Grip range.hef = Effective anchorage</p>
------	--

depth.Min. td =
Recommended
drilling depth.kN
= Load in kN.The
allowable load is
valid for one single
anchor, at cracked
concrete (tensile
zone) with concrete
class C20/25, incl.
partial safety factor
 $\gamma_f = 1,4$ and if the
Scr, N and Ccr,
N are taken in to
account.When
reduction on spacing
and edge distance
take place a re-
calculation of forces
should be carried out
by making use of the
technical guide or
calculation software,
they are available
on request.Final
calculations should
comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Specificatii tehnice

Desen tehnic

