



#urub cu cap torbant #i guler pătrat, par#ial filetat DIN 603 Alamă CU2/CU3 M5X70

Cod Articol	46050.050.070
Marcă	-
UBB	500648057114
UNSPSC	31161612
EAN	8717077289314
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Threaded pitch (P)	0.800
Diametru (d-D)	M5
Lungime (L) (mm)	70
Material (lung)	Alamă
Material tehnic	CU2/CU3
Direc#ie filet	Dreapta
Filete	Filet metric

Standarde

DIN	603
BS	≈4933
ISO	≈8677

Specificatii tehnice

b (min.): 125mm<L≤200mm	22
b (min.): L≤125mm	16
d _k (max.)	13.55
k (max.)	3.3
P	0.80
f _n (max.)	4.1
V _n (max.)	5.48

Desen tehnic

