



12X40 M10C

Cod Articol	47310FIS
Marcă	-
UBB	500616735915
UNSPSC	31162101
EAN	4006209473108
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Lungime	43 mm
Aprobare ETA	Yes
Info	do = Nominal diameter of drill bit.t = Recommended drilling depth.L (hef) = Effective anchorage depth.lsmin. = Screw-in depth min.lsmax. = Screw-in depth max.kN = Load in kN in combination with 8.8 & A4-70 bolts.Tinst = Tightening torque in Nm.The cone must be installed with setting tool type EAW H (narrow end) into the anchor body (article group 63322).Only part of the approval for light suspended ceilings.For further technical data the approval is available on request.

Standarde

Specificatii tehnice

Desen tehnic

FABORY

