

Șurub cu cap hexagonal complet filetat DIN 933 Oțel inoxidabil A4 (AD-W2) 70 pentru vase de presiune DIN 933 M10X35

Cod Articol	52511.100.035
Marcă	-
UBB	500697443371
UNSPSC	31161620
EAN	8715492060662
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Diameter	M10
Lungime	35 mm
Clasă	70
Tip antrenare	Hexagon
Forma de cap	Cap hexagonal
Material	Oțel inoxidabil
Material tehnic	A4 (AD-W2)
Filete	Filet metric

Info	Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W2, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are
------	---

Standarde

NF	E25-114
DIN	933
NEN	1568
ASME	B18.2.3.1M
ISO	4017

entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy. Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. for pressure vessels

Specificatii tehnice

d-D	M10
k	6.4
L (mm)	35
P	1.5
s	17

Desen tehnic

