



G 10/1

Cod Articol	65174FIS
Marcă	-
UBB	500616840699
UNSPSC	31161601
EAN	4006209651742
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Diameter	M10
Lungime	1000 mm
Info	Ccr, N = Characteristic Edge distance (tensile).Cmin. = Minimum edge distance (tensile).df = Hole diameter in fixture.do = Hole diameter in substrate.hef = Effective embedment depth.hmin = Minimum substrate thickness.ho = Minimum hole depth.Scr, N = Characteristic spacing.Concrete C20/25 recommended load for non-cracked concrete.The allowable load is only valid for AcryMaxx Chemical Mortar in combination with Anchor studs, steel grade 5.8.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete

Standarde

class C20/25, incl.
partial safety factor
 $\gamma_f = 1,4$ and if the
Scr, N and Ccr,
N are taken in
to account. Final
calculations should
comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Specificatii tehnice

Desen tehnic

