



M10

Cod Articol	90247FIS
Marcă	-
UBB	500616785175
UNSPSC	31161607
EAN	4006209902479
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Diameter	M10
Caracteristici cheie	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TA M can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l s : Screw length l s = Length of fixing + Thickness of fixture t fix + Thickness of washer.

Standarde

Aprobare ETA	Yes
Info	do= Nominal diameter of drill bit.dd= Embedment depth.df= Anchor diameter.fs= Head diameter.Ws= Setting tool

FABORY

diameter.hef=
Effective anchorage
depth.tfix= Grip
range.kN =
Allowable load in kN.

Specificatii tehnice

Desen tehnic

