



## KNIP LONG NOSE PL 30 3021-160MM

Cod Articol	K1030.120.160
Marcă	-
UBB	419100140203
UNSPSC	27112134
EAN	4003773035053
PKG. of 1	Exclusiv împachetare

### Parametri tehnici

Versiune	Vopsit negru & acoperite cu plastic
----------	-------------------------------------

Lungime totală 160

Remarci Heavy duty and wear resistant. Chrome Vanadium electric steel, oil-hardened and tempered. Style 1: long, trapezoidal jaws, serrated gripping surfaces. Style 2: long, half-round jaws, serrated gripping surfaces. Style 3: long, round jaws, smooth gripping surfaces. Finish 1 = Head polished. Handles plastic coated. Finish 3 = Plier chrome plated. Handles plastic coated. Finish 5 = Plier chrome plated. Handles with two-colour dual component sleeves. Finish 6 = Plier chrome plated. Handles insulated with two-colour dual component sleeves

### Standarde

ISO 5745

1000 V VDE-tested  
DIN EN/IEC 60900.

**FABUKY** *OF COURSE.*

SETTING THE STANDARD  
IN FASTENING SOLUTIONS