



KNIP RELAY ADJUST PL 37 3713-125MM

Cod Articol	K1037.310.125
Marcă	-
UBB	419100240292
UNSPSC	27112126
EAN	4003773043638
PKG. of 1	Exclusiv împachetare

Parametri tehnici

Versiune	Cromat & acoperite cu plastic
----------	----------------------------------

Lungime totală	125
----------------	-----

Remarci	Precision pliers for ultra fine assembly work, e.g. in electronics and fine mechanics. Chrome-Vanadium electric steel, oil-hardened and tempered. Style 1: flat, rectangular, concave jaws. Style 2: flat, pointed concave jaws. Style 3: half-round jaws. Style 4: round, pointed jaws to bend wire loops. Finish 1 = Head polished. Handles plastic coated. Finish 3 = Plier chrome plated. Handles plastic coated.
---------	---

Standarde

ISO	9655
-----	------