



#uruburi inbus cu cap bombat UNC ASME B18.3 Alloy steel ASTM F835 Simplu 1/4-20X2.1/2

Cod Articol	U07150.025.0250
Marcă	-
UBB	500620997881
UNSPSC	31161518
EAN	8715492888334
PKG. of 50	Exclusiv împachetare

Parametri tehnici

Diametru	1/4
Lungime (L) (Inch - ft)	2.1/2
TPI	20
Tip antrenare	Locaş hexagonal
Forma de cap	Cap bombat
Material tehnic	ASTM F835
Direc#ie filet	Dreapta
Tratament al suprafe#ei	Simplu

Standarde

ASME	B18.3
------	-------

Specificatii tehnice

A	0,437
H	0.132
J	5/32
Filete pe inch	20

Desen tehnic

