



Șuruburi ASME B18.6.3 cu cap rotund locaș crestat, filet UNC ASME B18.6.3 Oțel inoxidabil A2 (AISI 304/18-8) #4-40X3/16

Cod Articol	U51213.011.0018
Marcă	-
UBB	500625020622
UNSPSC	31161504
EAN	8717077798595
PKG. of 100	Exclusiv împachetare

Parametri tehnici

Diameter	NO.4
Lungime	3/16 Inch
Tip antrenare	Crestat
Forma de cap	Cap semirotund
Material	Oțel inoxidabil
Material tehnic	ASTM F837 304
Direcție filet	Dreapta
Filete	Unified National Coarse
Filete pe inch	40

Info

Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standarde

ASME B18.6.3

Specificatii tehnice

A (max.)	0.211
----------	-------

Desen tehnic

H (max.) 0.086

J (max.) 0.039

T (max.) 0.058

