



Assembly set for pressure vessels ISO 4014/4032 Ocel' Zinkované ponorením 5.6/5.2 M12X90

Číslo položky 08753.120.090

Značka -

UBB 500650921116

UNSPSC 31161620

EAN 8717077306585

PKG. of 50 Len kompletne
balenie

Technické parametre

Priemer	M12
Dĺžka	90 mm
Trieda	5.6/5.2
Vlastnosti nákrutky	Šestihran
Tvar hlavy	Šest'hranné
Materiál	Ocel'
Smer závit	Pravý
Vlastnosti povrchu	Zinkované ponorením
Závit	Metrický závit

Normy

ISO 4014/4032

Info Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-

Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy.

Technické špecifikácie

b (min.): 125mm $L \leq 200$ mm	36
b (min.): $L > 200$ mm	49
b (min.): $L \leq 125$ mm	30
d-D	M12
k	7.5
L (mm)	90
m (max.)	10.8
P	1.75
s	18

Technický nákres

