



Boutset voor drukvaten, voldraad ISO 4017/4032 Staal (AD-W7) Thermisch verzinkt 5.6/5.2 voor drukvaten M20X65

Artikelnummer 08762.200.065

Merk -

UBB 500648360138

UNSPSC 31161620

EAN 8717077245938

PKG. van 25 Alleen volledige
verpakkingen

Technische parameters

Diameter	M20
Lengte	65 mm
Klasse	5.6/5.2
Aandraaivoorziening	Zeskant
Kopsoort	Zeskantkop
Materiaalsoort	Staal (AD-W7)
Draadrichting	Rechts
Oppervlaktebedekking	Thermisch verzinkt
Draadsoort	Metrische schroefdraad

Info Specific features
of fasteners
for pressure
vessels: Intended
for use in pressure
vessels, steam
appliances,
equipment and
flange connections
at temperatures
from -10°C up
to +300°C. Meets
the requirements
of AD2000-W7,
TRD106 and DIN

Standaarden

ISO 4017/4032

267-13Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy.voor drukvaten

Technische specificatie

d-D	M20
k	12.5
L (mm)	65
m (max.)	18
P	2.5
s	30

Technische tekening

