



Svorníky so 2 šesťhrannými maticami UNC ASME B16.5/ B18.2.2 Nerezocel' ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 7/8X85 (3.3/8)

Číslo položky	22538.222.085
Značka	-
UBB	500578052077
UNSPSC	31161619
EAN	8715494332958
PKG. of 1	Len kompletne balenie

Technické parametre

Priemer	7/8 Inch
Dĺžka	85 mm
Trieda	Gr.B8M Cl.2 - Gr.8M
Materiál	Nerezocel'
Technický materiál	ASTM A193 - ASTM A194
Smer závit	Pravý
Závit	Unified National Coarse
Závitov na palec	9

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	--

Normy

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Technické špecifikácie

B	1.4375
---	--------

Technický náčrt

L (mm)	85
M	21.8

