



MaxxFast Šest'hranná hlava DIN ≈7504 K Bi-Metal ST5,5X45MM

Číslo položky	30420.055.045
Značka	-
UBB	500618373525
UNSPSC	31162400
EAN	8715494505925
PKG. of 200	Len kompletne balenie

Technické parametre

Priemer	5.5 mm
Dĺžka	45 mm
Vlastnosti nákrutky	Šestihran
Tvar hlavy	Šest'hranné
Materiál	Bi-Metal
Závit	Samorezný závit
Info	Len celé balenia.

Normy

ISO	≈15480
DIN	≈7504-K

Technické špecifikácie

dc (max.)	11
D (mm)	5.5
k (max.) - 30410	5.4
k (max.) - 30415	5.4
k (max.) - 30420	5.45
L (mm)	45
L1	6.5
s	8

Technický náčrt

