

10X40 M8



Číslo položky	47306FIS
Značka	-
UBB	500616735592
UNSPSC	31162101
EAN	4006209473061
PKG. of 100	Len kompletne balenie

Technické parametre

Dĺžka	43 mm
ETA-Certifikát	Yes
Info	do = Nominal diameter of drill bit.t = Recommended drilling depth.L (hef) = Effective anchorage depth.l_{smin.} = Screw-in depth min.l_{smax.} = Screw-in depth max.kN = Load in kN in combination with 8.8 & A4-70 bolts.T_{inst} = Tightening torque in Nm.The cone must be installed with setting tool type EAW H (narrow end) into the anchor body (article group 63322).Only part of the approval for light suspended ceilings.For further technical data the approval is available on request.

Normy

Technické špecifikácie

Technický náčrt

FABORY

