

Skrutka so šesťhrannou hlavou DIN 933 Nerezocel' A4 (AD-W2) 70 pre tlakové nádoby DIN 933 M10X25

Číslo položky	52511.100.025
Značka	-
UBB	500697443116
UNSPSC	31161620
EAN	8715492060648
PKG. of 100	Len kompletne balenie

Technické parametre

Priemer	M10
Dĺžka	25 mm
Trieda	70
Vlastnosti nákrutky	Šestihran
Tvar hlavy	Šesťhranné
Materiál	Nerezocel'
Technický materiál	A4 (AD-W2)
Závit	Metrický závit

Normy

ASME	B18.2.3.1M
DIN	933
NEN	1568
ISO	4017
NF	E25-114

Info	Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W2, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a
------	---

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy. Sizes with a
diameter M20 and
sizes with a length
8xd are minimal
property class 50.pro
tlakové nádoby DIN
933

Technické špecifikácie

d-D	M10
k	6.4
L (mm)	25
P	1.5
s	17

Technický náčrt

