



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M14X30

Article number	55050.140.030
Brand	-
UBB	951351816834
UNSPSC	31161605
EAN	8715492328878
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	30 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

ASME	B18.3.1M
ISO	4762
BS	4168-1
NF	E25-125
DIN	912
NEN	1241

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if L ≤	55
k (max.)	14
L (mm)	30
P	2
s	12

Technical Drawing

