



KIPP Clamping levers plastic grip, external thread Oranžová Nerezová ocel 1.4305 / plast M6X40X30

Číslo položky 58106.060.030

Značka -

UBB 500689756764

UNSPSC 31162807

EAN 4059245110698

PKG. of 5 Len kompletne balenie

Technické parametre

Farba	Orange
D1_MM	13mm
Materiál	Nerez/plast
Technický materiál	1.4305
Závit	Metrický závit

Info

For many people the Novo-Grip clamping lever represents the key to secure and comfortable gripping. This lever provides a future-oriented and powerful solution for almost any operating and clamping problem. Material: Handle fibreglass reinforced plastic with die-cast zinc toothed ring. Steel parts stainless steel 1.4305. Version: Steel parts bright.

Normy

Technické špecifikácie

A	40
A1	47

Technický náčres

B	7.5
D	10
D1	13
D2	14.5
H	24.5
H2	15
H3	30
H4	33.5
H1	4
Počet zubov	16
L	30
X	6

